



**PRODUCT DESCRIPTION**

A trendy two-tone Black and Gold low-profile flush mount to coordinate with the ever popular two-tone product designs throughout your project. The slim profile and stylish finish make this LED flush mount a dapper choice to pair with other Black and Gold furniture, furnishings, and plumbing options available. Available in two diameters 12" and 16" that house powerful LED light sources.

**MEASUREMENTS**

DIMENSION : 16" L x 16" W x 2" H  
 HANGING WEIGHT : 4.73 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 LUMENS : 2,250 Rated (1,700 Del.)  
 BULB : 1 x 25W LED AC Integrated , 25W Total  
 BULB INCLUDED : (Integrated)  
 DIMMABLE : Triac  
 CRI : 90 CRI  
 COLOR\_TEMP : 3000K  
 LIGHTING\_DIRECTION : Down

**FINISHES OPTION**

 Black / Antique Brass

**GLASS**

White WT

**MATERIAL**

Steel

**RATINGS**

cETLus  
 Damp Location  
 CA Title 24



**ADDITIONAL**

INSTALL UP/DOWN: UP  
 RATED LIFE 50000 Hours  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746  
 EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269  
 P. 626.956.4200 | F. 626.956.4225 | maximlighting.com