



PIG™ Microbial Oil Remediator for Soil, Grass and Water

CLN936 Remediator, 1 gal. Container, 1 each

Break down and eliminate oil and fuel on soil, grass and water with our stormwater-safe solution. Environmentally friendly formula requires no containment or cleanup!

- Gradually remove oil and fuel from soil, grass and water to eliminate rain runoff
- BioBreaker microbes digest hydrocarbons through bioremediation, naturally converting them into water and harmless gases
- Stormwater-safe solution can enter storm drains without harming the environment
- Easier than using cleaners and degreasers that cannot be allowed into waterways or groundwater systems — just check the SDS, Section 6, on competitor cleaners to see the warning!
- Applies easily using a manual sprayer; product is designed to work over time as a repeated application
- Product is concentrated and must be diluted 10:1; each diluted gallon will remediate approximately one cubic yard of soil or 200 gallons of water



Specifications

Style	Remediator
Brand	PIG
Intended Use	Soil and Water
Temperature Limit	Works from 42°F (5.5°C) to 120°F (49°C)
Treats	Treats 2,000 gal. or up to 10 cu. yds.
Volume	1 gal. Container
Color	Green
VOC Content	VOC-Free
Sold as	1 each
Weight	8.8 lbs.
# per Pallet	60
Composition	Water 89%

Alkypolyglycoside 6%

Bacterial Cultures 5%

Green Dye

Shelf Life

2 years

UNSPSC

47131821

Metric Equivalent

Weight

4 kg

Technical Information

USOnly

This product can ONLY be shipped to the United States.

Technical Documents

[Technical Data Sheet for PIG® Microbial Oil Remediator for Soil, Grass and Water](#)



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com