

PIG® Caution Industrial Absorbent Adhesive-Backed Grippy® Floor Mat

MAT32400 Absorbs Oils; Coolants; Solvents; Water; Universal, 32" x 100', 1 roll



Alert workers to slip or trip hazards around workstations and machinery with a high-visibility adhesive-backed absorbent mat featuring a repeating caution message; provides traction and safe footing in slip prone areas.

- Bright yellow color and caution message draw attention to potential slip hazards from leaks and drips around machinery, equipment, workstations and production areas, even in poorly lit areas
- Adhesive-backed mat stays exactly where you put it with no shifting, bunching up or flipping over to prevent slips, trips and falls
- Sticks to most commercial floor surfaces like cleaned and sealed concrete, vinyl tile, linoleum, ceramic tile and quarry tile
- Walk all over it! Tough, spunbond top layer with heavy-duty zigzag stitching stands up to foot and light-wheeled traffic; keep mat in service until it's saturated or shows signs of wear
- Makes it easy to sweep up debris like metal shavings and wood chips while also absorbing common industrial fluids
- Multiple layers of fine-fiber polypropylene safely absorb leaks, drips and overspray of oils, coolants, solvents and water to keep them from being tracked around
- Leakproof backing prevents absorbed liquid from soaking through to the floor for easier change outs and floor protection
- Easy to cut and install: just roll it out, cut to size, stick it down and apply pressure to smooth it out
- Align seams end to end or side by side to cover large areas; do not overlap seams to avoid premature lifting
- Proprietary adhesive sticks to the floor with a super-tight grip, but peels up easily for quick changeouts; reduces cleanup time to make your facility more productive
- Tested and Certified by the National Floor Safety Institute (NFSI): when used as part of your floor safety program, high-traction surfaces such as PIG Caution Grippy Mat have been proven to reduce slip-and-fall claims by as



much as 90%

- Mats take on the properties of absorbed liquids
- always take proper precautions when handling saturated absorbents



Item#	Description	Dimensions	Weight
MAT32400-YW		32" W x 100' L	31 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
MAT32400-YW		81cm W x 30m L	14.1 kg

Specifications

Absorbency Range	10 - 19.9 gal.
Dimensions	32" W x 100' L
Mat Weight	Mediumweight
Recycled Content	25% or more Recycled Content
Absorbency	Up to 10.5 gal. per roll
Brand	PIG
Category	Grippy® Industrial Absorbent Mat
Flammability Specifications	Flame Resistant - Will melt and self-extinguish
Fluid Absorbed	Oils; Coolants; Solvents; Water; Universal
Incinerable	Yes
Industry	Industrial Facilities; Shops & Garages
Intended Use	Indoor Use on Concrete, Vinyl, Linoleum, Tile and Laminate Flooring
Perforated	No
Storage Temp Range	Store between 32°F and 120°F
Temperature Limit	Surface temps from 55°F to 120°F
Traffic	Light Foot Traffic
UV Resistant	No
Sold as	1 roll
Weight	31 lbs.
New Pig Patent	Patent Pending
# per Pallet	12

Composition
Absorbent: Polypropylene
Stitching: Polyester

UNSPSC

47131901

Pigalog® Page Number

Page 25

Metric Equivalent

Absorbency

Up to 39.7 L per roll

Weight

14.1 kg

Dimensions

81cm W x 30m L

Technical Information

Certifications, Approvals and Ratings

NFSI Certified,ANSI B101.1- 2009,ANSI/ESD STM11.11,MIL-STD-3010C

Technical Documents

[PIG Grippy® Absorbent Mat](#)

[The Complete Slip, Trip & Fall Risk Zone Audit](#)

[New Pig Adhesive-Backed Mat Notice](#)

[How to use PIG Grippy Absorbent Mat](#)

[Instructions for PIG Grippy Mat Cleaning & Care Guide](#)

[Static Coefficient Of Friction \(SCOF\) Testing](#)

[White Paper- Getting a Grip on Slips, Trips and Falls](#)

[White Paper- The Walk Zone Safety Report](#)

[PIG® Grippy® Absorbent Mats](#)

[29 CFR 1910.22\(a\)\(2\)](#)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com