

PIG® HazMat Chemical Absorbent Mat Roll

MAT3600 Lightweight, 15" x 50', 6 rolls per box



Safely soak up acids, bases, corrosives and hazardous chemical spills with our HazMat absorbent mat rolls.

- Clean up leaks and spills of hazardous liquids in chemical storage areas, on workbenches, counters and shelves with our lightweight rolls
- Soak up the widest range of acids, bases, corrosives, chemicals and unknown liquids - even those with high concentrations like 98% sulfuric acid and 30% sodium hydroxide
- Absorbs a wide range of hazardous liquids found in chemical storage areas, around dip tanks, in cleaning agents used in food processing plants, in boiler rooms, labs, and R&D departments
- Pink color is designated for hazardous chemicals and easy to identify in a spill emergency or cleanup
- Chemical-resistant mat won't degrade or cause a dangerous reaction upon contact with corrosive spills
- PIG Mat lasts 2x longer than competitive mats and won't rip, tear or fray even when saturated; liquids absorb quickly for faster, easier cleanups and safer workplaces
- Mats take on the properties of absorbed liquids
 - always take proper precautions when handling saturated absorbents



Specifications

| | |
|------------------|-------------------------|
| Absorbency Range | 10 - 19.9 gal. |
| Dimensions | 15" W x 50' L |
| Mat Weight | Lightweight |
| Absorbency | Up to 19.8 gal. per box |
| Absorbency per | Up to 3.3 oz. per roll |
| Brand | PIG |
| Color | Pink |
| Core Diameter | 1.5" |

| | |
|------------------------------------|---|
| Flammability Specifications | Flame Resistant - Will melt and self-extinguish |
| Floating | No |
| Fluid Absorbed | Acids; Bases; Unknowns |
| Indoor/Outdoor | Indoor Use |
| Incinerable | Yes |
| Perforated | Yes |
| Perforated Pattern | 10" x 15" sections |
| Reusable | No |
| Static-Dissipative | No |
| Traffic | Not Recommended for Foot Traffic |
| UV Resistant | No |
| Wringable | Yes |
| Sold as | 6 rolls per box |
| Weight | 17 lbs. |
| # per Pallet | 24 |
| Composition | Polypropylene |
| UNSPSC | 47131901 |
| Pigalog® Page Number | Page 69 |

Metric Equivalent

| | |
|-----------------------|------------------------|
| Absorbency per | Up to 97.6 mL per roll |
| Absorbency | Up to 74.9 L per box |
| Weight | 7.7 kg |
| Dimensions | 38cm W x 15.2m L |

Technical Information

Technical Documents

[PIG Hazardous Chemical Absorbents](#)

[Technical Data Sheet for PIG® HazMat Absorbents](#)

[29 CFR 1910.22\(a\)\(2\)](#)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com

