

PIG® 2-Drum Poly Deck with Pallet Jack Pockets

PAK1020 Holds (2) 55 gal. Poly or Steel Drums, 26" x 52" x 6.5", Sump Capacity 22 gal.

No forklift required! Just slide your pallet jack right in to easily transfer drums on this drip-catching deck.

- Fork pockets are spaced to fit most pallet jacks; deck can be moved fully loaded with properly secured drums (straps not included)
- 2,000 lb. UDL capacity is strong enough to support two fully loaded steel or poly drums; Decks will never buckle or bow
- Low-profile 6.5"H design is easy to load or unload; pumps and funnels are easy to access
- 22-gallon sump catches leaks, drips and spills during drum transfers
- Low-density polyethylene (LDPE) construction resists UV rays, rust, corrosion and most chemicals
- Textured grating adds traction and lifts out for easy sump access



Item#	Description	Dimensions	Weight
PAK1020-WOD	Without Drain	26" W x 52" L x 6.5" H	49.5 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK1020-WOD	Without Drain	66cm W x 132cm L x 17cm H	22.5 kg

Specifications

Sump Capacity Range	20 - 39.9 gal.
Dimensions	26" W x 52" L x 6.5" H
Load Capacity UDL	2000 lbs.
Sump Capacity	22 gal.
Brand	PIG
Drain	None
Color	Black
Double-Stackable Unit	No
Grates	(1) 48" L x 24" W Grate

Fork Truck Access

Two-Way Fork Access, Can Move Loaded (Not Double-Stacked)

Holds	(2) 55 gal. Poly or Steel Drums
Material	Poly
Use With Flammables	No
Sold as	1 each
Weight	49.5 lbs.
# per Pallet	6
Composition	Sump: Polyethylene (LDPE) w/ UV Inhibitor Grate: Polyethylene
UNSPSC	24101905
Pigalog® Page Number	Page 352

Metric Equivalent

Sump Capacity	83.3 L
Load Capacity UDL	907.2 kg
Weight	22.5 kg
Dimensions	66cm W x 132cm L x 17cm H

Technical Information

Technical Documents

LDPE Products

Pocket Dimension Measurements

40 CFR 112.7

40 CFR 122.26

40 CFR 264.175



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com