

PIG® 1-Drum Foam Wall Spill Berm

PAK851 Ideal For Portable Drum Containment, 30" x 30" x 4", Sump Capacity 8 gal.

Portable soft wall berm contains leaks and spills from stored containers – you don't need a ramp to load drums!



- 4"-high foam sidewalls can be driven over with a drum truck and spring back; eliminates the need for expensive and bulky ramps
- High-visibility green sidewalls are easy to see; reduce risk for trips
- Heavy-duty, 22 oz. vinyl provides resistance to tears, punctures and chemicals
- Lightweight, portable unit folds up for easy transport and sets up in seconds
- Economical alternative to hard plastic pallets and decks
- Removable polyethylene grate keeps drums out of liquid
- Perfect for temporary storage of drums, machine parts, tanks and generators or as washdown pad
- Helps you meet hazardous waste containment regulations (depending on the size of containers stored)

Specifications

Sump Capacity Range	1 - 9.9 gal.
Dimensions	30" W x 30" L x 4" H
Sump Capacity	8 gal.
Brand	PIG
Drain	None
Grates	(1) 24" L x 24" W Grate
Color	Black/Green
Holds	(1) 55 gal. Poly or Steel Drum
Ideal For	Portable Drum Containment
Traffic	Cart Traffic
Sold as	1 each
Weight	18.15 lbs.
Composition	Berm: 22 oz. Vinyl Grate: HDPE

Includes

- 1 - 30" L x 30" w Sump (PAK856)
- 1 - 24" L x 24" W Grate (PAK850)

Metric Equivalent

Sump Capacity

30.3 L

Weight

8.2 kg

Dimensions

76cm W x 76cm L x 10cm H

Technical Information

Technical Documents

[PIG Soft-Sided Berms](#)[40 CFR 112.7](#)[40 CFR 122.26](#)[40 CFR 264.175](#)**New Pig**

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-03041-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com