

Bradley® Faucet-Mount Eye Wash

PLS1615 Faucet Mount; Plumbed, Flow Rate 0.4 gal./Minute

Turn any faucet near high-risk areas into an emergency eye wash station

- Universal mount connects eye wash to any standard or gooseneck faucet to provide an unlimited water supply
- Versatile design won't interfere with normal sink operation; water flows straight through until knob is pulled to activate eye wash
- Twin spray heads include pop-off plastic dust caps to keep out contaminants
- Integral flow control produces a safe, steady flow of water at 0.4 gpm; regulates varying water supply conditions from 30 to 90 psi
- Chrome-plated brass construction resists corrosion and provides a clean, mirrored finish
- Includes universal signage and inspection tag to help identify and encourage maintenance of eye wash



Specifications

Style	Faucet Mount; Plumbed
Brand	Bradley
Capacity	Unlimited
Dispensing Method	Plumbed
Flow Rate	0.4 gal./Minute
Sold as	1 each
Color	Silver
Weight	1.08 lbs.
Composition	Chrome-Plated Brass
Includes	1 - Emergency Sign 1 - Inspection Tag 1 - Mounting Hardware 1 - Eyewash Unit
UNSPSC	46181810

Pigalog® Page Number

Page 205

Metric Equivalent

Weight

.5 kg

Technical Information

Certifications, Approvals and Ratings

ANSI Z358.1-2014

Technical Documents

29 CFR 1910.151(c)



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com