

PIG® Light-Duty Solvent Wipers

WIP191 Pop-Up Wipers, 9.625" x 16", 750 wipers (6 boxes of 125 each)

Made binder-free to excel at wipe-downs with solvents like alcohol and MEK. Low-lint blend provides ideal wipe-dry during printing tasks. Pull from a convenient pop-up box.

- Easily pull one at a time from the convenient pop-up box
- Low-lint cellulose/polyester blend is ideal for the printing industry because of excellent wipe-dry properties
- Binder-free construction is specifically designed to resist solvents and degradation
- Soft, durable, textured surface gives a comfortable, clothlike feel
- Absorbs oils, grease, water and solvents during degreasing and cleaning
- Want to try out a new specialty wiper? Your satisfaction is always guaranteed with the PIG Promise... try a case risk-free!



Specifications

Style	Pop-Up Wipers
Dimensions	9.625" W x 16" L
Application	Printing Press; Low-Lint
Brand	PIG
Dispenser	Yes
Strength Rating	No Strength Rating
Color	White
Sold as	750 wipers (6 boxes of 125 each)
Weight	13.8 lbs.
# per Pallet	36
Composition	Cellulose & Polyester Blend
UNSPSC	47131502
Pigalog® Page Number	Page 136

Metric Equivalent

Weight	6.3 kg
--------	--------

Dimensions

24cm W x 41cm L

Technical Information



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com