

WorkWipes® Series 60 Wipers

WIP662 Pop-Up Wipers, 16" x 8", 990 wipers (9 boxes of 110 each)

Here's great value for you - lower-cost PR60 wipers that can handle many heavy-duty jobs.

- Great value for fast cleanups - these are tougher than general-purpose and maintenance wipers but the lightest of the heavy-duty wipers
- Cellulose-polypropylene blend for strength, low lint and a unique "stretch" for wiping jagged parts without tearing
- Textured surface helps remove dirt and grime quickly
- Useful for a range of jobs - from applying disinfectants, degreasers and solvents to cleaning hands, glass or stainless steel
- Low-profile pop-up boxes are better suited for workstations and tool carts than larger, bulkier options
- Low-lint construction won't shed, pill or leave behind unwanted fibers when wiping parts
- Binder-free construction withstands solvents, degreasers and cleaning agents
- Want to try out a new wiper? Your satisfaction is always guaranteed with the PIG Promise... try a case risk-free!



Specifications

Style	Pop-Up Wipers
Dimensions	16" W x 8" L
Application	Heavy Duty; Low-Lint
Brand	WorkWipes
Dispenser	Yes
Strength Rating	Heavy-Duty
Color	White
Sold as	990 wipers (9 boxes of 110 each)
Weight	14.9 lbs.
# per Pallet	36
Composition	Polypropylene & Cellulose Blend
UNSPSC	47131502

Metric Equivalent

Weight

6.8 kg

Dimensions

41cm W x 20cm L

Technical Information

**New Pig**

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-03041-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com