

WorkWipes® Series 60 Wipers

WIP663 Pop-Up Wipers, 12" x 8", 990 wipers (9 boxes of 110 each)

Here's great value for you - lower-cost PR60 wipers that can handle many heavy-duty jobs.

- Great value for fast cleanups - these are tougher than general-purpose and maintenance wipers but the lightest of the heavy-duty wipers
- Cellulose-polypropylene blend for strength, low lint and a unique "stretch" for wiping jagged parts without tearing
- Textured surface helps remove dirt and grime quickly
- Useful for a range of jobs - from applying disinfectants, degreasers and solvents to cleaning hands, glass or stainless steel
- Low-profile pop-up boxes are better suited for workstations and tool carts than larger, bulkier options
- Low-lint construction won't shed, pill or leave behind unwanted fibers when wiping parts
- Binder-free construction withstands solvents, degreasers and cleaning agents
- Want to try out a new wiper? Your satisfaction is always guaranteed with the PIG Promise... try a case risk-free!



Specifications

| | |
|-----------------|----------------------------------|
| Style | Pop-Up Wipers |
| Dimensions | 12" W x 8" L |
| Application | Heavy Duty; Low-Lint |
| Brand | WorkWipes |
| Dispenser | Yes |
| Strength Rating | Heavy-Duty |
| Color | White |
| Sold as | 990 wipers (9 boxes of 110 each) |
| Weight | 12.8 lbs. |
| # per Pallet | 27 |
| Composition | Polypropylene & Cellulose Blend |
| UNSPSC | 47131502 |

Metric Equivalent

Weight

5.8 kg

Dimensions

30cm W x 20cm L

Technical Information

**New Pig**

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-03041-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com