

## Disposable Latex Response Boots

WPL241 Overboot, 12" High

Customer favorite for fast, disposable chemical splash protection.

- High-quality boots fit over other boots/shoes to add protection from acids, alcohols and salts
- Features smooth inside finish for easy on/off and non-skid sole for use on smooth surfaces
- Disposable yellow latex boots are .60 mm gauge rubber for reliable performance without rips or tears
- Pairs are individually packaged for easy storage and fast access in emergencies
- Great addition to spill response training that fits easily into spill kits
- NOTE: Men's sizes only; women should order two sizes smaller



Item#	Description	Dimensions	Weight
WPL241-L	Large		.6 lbs.
WPL241-XL	X-Large		.6 lbs.
WPL241-XXL	XX-Large		.6 lbs.

### Metric Equivalent:

Item#	Description	Dimensions	Weight
WPL241-L	Large		.3 kg
WPL241-XL	X-Large		.3 kg
WPL241-XXL	XX-Large		.3 kg

### Specifications

Style	Overboot
Brand	Dunlop Onguard
Reusable	No
Shoe Height	12" High
Sizing	L (7-9), XL (10-12), XXL (13-16) in Men's Sizes
Toe Type	Standard
Color	Yellow
Sold as	1 pair
Weight	.6 lbs.

**Composition**

Latex Rubber

**UNSPSC**

46181602

**Pigalog® Page Number**Page 189**Metric Equivalent****Weight**

.3 kg

**Technical Information****CountryNoShip**

This product is subject to export restrictions and cannot be shipped to the European Union or Great Britain.

**Technical Documents**

Onguard Industries Disposable Latex Response Boots

29 CFR 1910.132

**New Pig**

World's best stuff for leaks, drips and spills.

**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com