



## North Butyl Gloves

WPL265 Thickness 16 mil, 11", 1 pair

Sure-grip palms and excellent permeation resistance are a great combination for working with parts dipped or coated in toxic liquids.

- Highest permeation resistance to gas and water vapor for safer handling of toxic substances like ketones and esters
- Fingers and hand are curved for comfort
- Butyl is flexible and sensitive even at lower temperatures
- Rough Grip-Saf palm offers a better grip on wet or oily parts



Item#	Description	Dimensions	Weight
WPL265-8	Size 8	11" L	
WPL265-9	Size 9	11" L	
WPL265-10	Size 10	11" L	
WPL265-11	Size 11	11" L	

### Metric Equivalent:

Item#	Description	Dimensions	Weight
WPL265-8	Size 8	28cm L	
WPL265-9	Size 9	28cm L	
WPL265-10	Size 10	28cm L	
WPL265-11	Size 11	28cm L	

### Specifications

Style	Chemical-Resistant
Dimensions	11" L
Brand	Honeywell North
Coating	None
Cuff	Beaded
Lining	None
Color	Black

<b>Primary Material</b>	Butyl
<b>Thickness</b>	16 mil
<b>Texture</b>	Rough
<b>Sold as</b>	1 pair
<b>Composition</b>	Butyl
<b>UNSPSC</b>	46181504

## Metric Equivalent

<b>Dimensions</b>	28cm L
-------------------	--------

## Technical Information

### Technical Documents

North Butyl Gloves

29 CFR 1910.132

29 CFR 1910.138



**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • [newpig.com](http://newpig.com) • [hothogs@newpig.com](mailto:hothogs@newpig.com)