

SHOWA Nitri-Solve® Nitrile Gloves

WPL587 Thickness 11 mil, 13", 1 pair

Tough nitrile offers excellent resistance to long-term submersion in many chemicals.



- Nitrile material stands up to long-term submersion in many harsh chemicals, including 30% hydrogen peroxide, ethylene glycol, gasoline and diesel fuel
- Reusable gloves won't swell, degrade or expose hands to potential irritation and injury
- Left- and right-hand molds are curved to match hand contours for minimized fatigue
- Embossed texture adds grip when handling wet or oily objects
- Extra-long cuff extends protection past wrist onto forearm
- Great for spill response, degreasing, solvent washing, painting, acid dipping, oil refining and more



Item#	Description	Dimensions	Weight
WPL587-08	Size 8	13" L	.15 lbs.
WPL587-09	Size 9	13" L	.15 lbs.
WPL587-10	Size 10	13" L	.15 lbs.
WPL587-11	Size 11	13" L	.15 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
WPL587-08	Size 8	33cm L	68 g
WPL587-09	Size 9	33cm L	68 g
WPL587-10	Size 10	33cm L	68 g
WPL587-11	Size 11	33cm L	68 g

Specifications

Style	Chemical-Resistant
Dimensions	13" L
Brand	SHOWA
Coating	None
Cuff	Gauntlet

Lining	None
Color	Green
Primary Material	Nitrile
Thickness	11 mil
Texture	Rough
Sold as	1 pair
Weight	.15 lbs.
Composition	Nitrile
UNSPSC	46181504
Pigalog® Page Number	<u>Page 193</u>

Metric Equivalent

Weight	68 g
Dimensions	33cm L

Technical Information

Technical Documents

SHOWA Gloves

SHOWA Nitri-Solve® Nitrile Gloves

29 CFR 1910.132

29 CFR 1910.138



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com