

HazProof™ Boots

WPL672 Boot, 11" High

Specific sizing with unique closure means fast on/off and a secure fit.

- State-of-the-art design and construction maximize protection against hazardous chemicals
- Made of special polymer compound with steel toe and midsole for excellent protection against penetration
- Sure-grip sole provides traction on wet, slippery surfaces
- Unique closure system catches and releases quickly, even with gloves
- Large foot area makes on/off easy, even when used with bulky encapsulated suit
- Exceeds NFPA 1991 and 1994 requirements for chemical permeation and flammability
- Sizing corresponds to standard men's shoe sizes to eliminate ordering guesswork



Item#	Description	Dimensions	Weight
WPL672-10	Size 10		7 lbs.
WPL672-11	Size 11		7 lbs.
WPL672-12	Size 12		7 lbs.
WPL672-13	Size 13		7 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
WPL672-10	Size 10		3.2 kg
WPL672-11	Size 11		3.2 kg
WPL672-12	Size 12		3.2 kg
WPL672-13	Size 13		3.2 kg

Specifications

Style	Boot
Brand	Tingley Rubber
Reusable	Yes
Shoe Height	11" High

Toe Type	Steel Toe
Sold as	1 pair
Color	Orange
Weight	7 lbs.
Composition	Polymer Compounds
UNSPSC	46181602
Pigalog® Page Number	<u>Page 188</u>

Metric Equivalent

Weight	3.2 kg
---------------	--------

Technical Information

CountryNoShip

This product is subject to export restrictions and cannot be shipped to the European Union or Great Britain.

Technical Documents

Tingley® Hazproof

29 CFR 1910.132

29 CFR 1910.136



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com