



Empowering you to work smarter

NRRD Recovery Unit



Light • Fast

One Key Operation

- Easy to use

Twin Cylinder

- Fast recovery

Oil-Free Compressor

- Suitable for all commonly used refrigerants

Purge Function

- Prevent mixing of various refrigerants

High Pressure Protection

- Added safety

| Model | | NRRD | | | |
|---------------------------|---------|---|--------|-------|--------|
| Refrigerant Type | | Category III: R-12, R-134a, R-401C, R-500 Category IV: R-22, R-401A, R-401B, R-402B, R-407C, R-407D, R-408A, R-409A, R-411A, R-411B, R-412A, R-502, R-509 Category V: R-402A, R-404A, R-407A, R-407B, R-410A, R-507 | | | |
| Power Supply | V/Hz | 115V/60Hz | | | |
| Motor | HP | 1 | | | |
| Max Current Draw | A | 10 | | | |
| Compressor | | Oil-less, Air-cooled, Piston style | | | |
| Automatic Safety Shut-Off | | 558 psi/38.5 bar | | | |
| Recovery Rate | lbs/min | | R-410A | R-22 | R-134a |
| | | Direct Vapor | 0.44 | 0.49 | 0.31 |
| | | Direct Liquid | 6.06 | 6.17 | 4.7 |
| | | Push/Pull Liquid | 12.61 | 11.60 | 10.8 |
| Dimension | in | 18 x 10 x 14 | | | |
| Weight | lbs | 30 | | | |

1-YEAR WARRANTY

www.navacglobal.com