

# NOBLELIFT

INDUSTRIAL EQUIPMENT

## AC55 Series | Manual Pallet Jack with Nylon Wheels






**PREMIUM PALLET JACK**

**Best Seller Worldwide**

# NOBLELIFT

## Weight Capacity: 5500 lbs.



WHY CHOOSE BETWEEN PRICE AND QUALITY WHEN YOU CAN HAVE BOTH

## PREMIUM PALLET JACK

- Top class range of pallet trucks with excellent ergonomic designs .
- Professional and ideal storage aid for all variety of manual transport tasks over short distances in stores, warehouses and factory plants .
- Reliable, sturdy, torsion-resistant due to its extremely strong high quality steel profile . German WAGNER paint system ensures best powder coating and painting quality .
- All pivots points are greased for excellent maneuverability and effortless steering. Chromed bearing bushes and joints ensure quiet running application and particularly long service life .
- High quality galvanized whole casting hydraulic pump, robust and durable, with fine control of lowering speed, overload valve, and low maintenance

## AUTHORIZED DEALER

Item/Type		AC55-2748NW
Capacity Q	lbs	5500
Min. fork height h	Inch	2.95"
Max. fork height h <sub>1</sub>	Inch	7.5
Steering wheel	Inch	φ 2"×7" φ O.D:2.75 W:3.7
Load roller Single	Inch	
Size of fork e*s	Inch	6.3×2.4
Width overall forks B	Inch	27"
Fork length l	Inch	48"
Special sizes under request		
Optional fork width	Inch	
Optional fork length	Inch	