NIO-2RTLA Type 2" Iolite Round Trimless Adjustable Project Source: 14W LED Catalog No. 800lm or 1000lm Notes PRODUCT IMAGES AND DIMENSIONS PRODUCT DESCRIPTION 2" Trimless lolite downlights have no exposed trim flange and do not extend beyond the ceiling plane. lolite Trimless requires a Trimless Mud Ring and New Construction housing. Regressed cone reflector optimizes visual cut-off and adjust up to 15°. FEATURES Trimless knife edge appearance Adjustable finish Reflector finish 800lm or 1000lm LED packages . 2-3/4" Comfort Dim (warm dimming) also available in 800lm only 2700K, 3000K, 3500K, 4000K or 5000K @ 90+ CRI . Flood optic, narrow flood and spot optics (included) NIO-2RTLA Round Trimless Adjustable 5-Year limited warranty 15° Adjustable SPECIFICATION Construction: Trims are constructed of heat dissipating, die-cast aluminum. The aluminum die-cast LED heat sink is threaded to fit trimless downlight and transfer heat. Mounting: Luminaire includes friction blades to mount securely to trimless mud ring. A trimless mud ring is required per BB BW trimless downlight. Black Adjustable Black Adjustable Black Reflector White Reflector OPTICS 800-1000im: Three field changeable optics (spot, narrow flood and flood) are included with each LED module. Premium 10° TIR narrow spot optic assembly also available (Click Here for more information). Optional frosted and TIR optics are also available. ELECTRICAL Lumens / Wattage: 800lm / 14W, 1000lm / 14W BZ CH Color Temperature: 2700K, 3000K, 3500K, 4000K, 5000K Bronze Adjustable Champagne Haze Adjustable Color Rendering Index: 90+CRI Bronze Reflector Champagne Haze Reflector Operating Temperature: Specified by housing Lifetime: 50,000 hours @ L70 Comfort Dim: Comfort Dim color tunes the temperature from a bright 3100K, to a romantic and comfortable 2000K on a gradual, even curve. Available in 800lm only. Dimming: Specified by housing CHMPW HW **COMPATIBLE HOUSINGS** Champagne Haze Adjustable Haze Adjustable Luminaires are compatible with respective lolite housings manufactured by Nora Lighting. Matte Powder White Reflector White Reflector CATALOG NO. DESCRIPTION LUMENS / WATTAGE NHIOICD-28 ICAT New Construction 800-1000lm / 14W 800-1000lm / 14W Chicago Plenum NHIOICDCP-28 Accessories: Luminaires will accommodate (1) hex louver and (1) translucent deco collar or opaque snoot, no accessory holder is required, see accessories page. A trimless mud ring is required per reflector. H7 H7MPW Haze Adjustable Haze Adjustable LABELS AND LISTINGS Haze Reflector Matte Powder White Reflector cULus Listed for Damp Locations ENERGY STAR certified . 5-Year Limited Warranty **RoHS** Compliant Certified to the high efficacy requirements of California Title 24 JA8-2022 MPW ww ()omfort**Dim**® Matte Powder White Adjustable White Adjustable Matte Powder White Reflector White Reflector 2" Iolite Round Trimless Adjustable - New Construction Housing & Trimless Mud Ring Required **Compatible Housings** Reflector Type Finish Lumens / Wattage Housing Type Color Temp NIO-2RTLA = Round Trimless Adjustable NHIOICD-28 = ICAT New Construction / 800-1000lm / 14W 50X = 5000K* BB = Black (blank) = 800lm / 14W CDX = Comfort Dim⁴ BW = Black / White NHIOICDCP-28 = Chicago Plenum / 800-1000lm / 14W BZ = Bronze 27X = 2700K /10 = 1000lm / 14W 2" lolite Trimless Mud Ring CH = Champagne Haze **30X** = 3000K CHMPW = Champagne Haze / Matte Powder White **35X** = 3500K Description HW = Haze / White **40X** = 4000K NIO-TLMR-2RA = 2" Round Trimless Mud Ring HZ = Haze 50X = 5000K HZMPW = Haze / Matte Powder White MPW = Matte Powder White WW = White

* 5000K LED modules in 800lm are while supplies last

⁺ Comfort Dim available in 800Im only and 1" lolite uses a different dimming curve than 2" & 4" lolite

Example: NIO-2RTLA50XWW / NIO-TLMR-2R = 2" lolite Round Trimless Adjustable, 5000K, White finish, 800lm / 2" Round Trimless Mud Ring

NORA

6505 Gayhart Street, Commerce, CA 90040 TEL 323.767.2600 | www.noralighting.com | e-mail: nora@noralighting.com © 2023 Nora Lighting, Inc. All rights reserved. Specifications subject to change without notice. 2" Iolite Round Trimless Adjustable

Type Project Catalog No. Notes


FIELD CHANGEABLE OPTICS

lolite luminaires include spot, narrow flood and flood optics. Optics can be changed in the field by removing LED module from die-cast trim. Replacement optics include an optional frosted lens.



ACCESSORIES

lolite accessories can be added at any point in the design process. Accessories easily install between LED module and die-cast trim. Luminaire will accommodate (1) hex louver and (1) collar accessory, no accessory holder required.





Translucent Decorative Collar

AM (amber), BLU (blue), FR (frosted), R (red)

Translucent collars color the aperture

with the specified color while producing

white general light. Collars are available

in different lengths. Use to add interest, create a theme, match a theme or define

NIO-AS14(color)

NIO-AS19(color)

NIO-AS26(color)

<u>Color</u>:

a space.

Opaque Collar Snoot

NIO-AS14(color)	5∕8" le
NIO-AS19(color)	3⁄4" le
NIO-AS26(color)	1" le
Color:	
MPW (matte powder whit	e), WH (white)

Opaque snoot greatly reduces aperture brightness while preserving light output.



Hex Cell Louver

ength ength ength	NIO-HC	Black
	Hex cell louver subtly reduces aperture brightness by reducing light output by about 20%.	

Hex cell louver is not compatible with TIR optics.

TRIMLESS

2" lolite trimless downlights have no exposed trim flange and the result is a minimalist knife edge appearance. A trimless mount mud ring is installed after the drywall and a professional drywall finisher floats the ceiling to blend in the mud ring.

5∕%" length

3⁄4" length

1" lenath





Trimless Mount Mud Ring

NIO-TLMR-2RA

Mounts trimless downlight with no exposed flange and no extension beyond ceiling plane. Mud ring attaches to drywall. Only for use with NHIOICD-28 or NHIOICDCP-28 new construction housings and NIO-2RTLNDC or NIO-2RTLA. Dimensions: 7-1/8" diameter 1/2" thick



Suction Cup for Removal

NIO-TLSUCTION

Assist removing trimless reflector from finished ceiling after installation. For maintenance on trimless reflector.