NS-44 / NS-46 / NS-52 / NS-53

4" Reflector with Ring

Type
Project
Catalog No.
Notes

FEATURES

Trim: Precision spun 0.050 aluminum high grade reflector. Separate trim ring available in metal, may also be used with custom combination of plastic or metal ring finishes.

Mounting: Trim includes three trim clips that securely mount trim in housing.

COMPATIBLE HOUSINGS

Compatible with line voltage and GU24 housings. See individual specification sheets for more information.

LAMP

Line Voltage:

15W R20/PAR20 max. (NS-401AT/IC)
35W R20/PAR20 max. (NFBIC-4INCATA)
50W R20/PAR20 max. (NS-4010AT; NSIC-4010AT; NSR-4040AT; NSRIC-4040AT)

GU24:

26W GU24 max. (NHIC-4G24AT)

See individual housing specification sheets for more information.

LABELS AND LISTINGS

cULus Listed for Damp Location when used with compatible housing.






PRODUCT IMAGES & DIMENSIONS











4" Reflector with Ring

Catalog No.

NS-44 = 4" Specular Clear Reflector with White Metal Ring

NS-44HZ = 4" Haze Reflector with White Metal Ring

NS-46 = 4" Specular White Reflector with White Metal Ring

NS-52 = 4" Natural Metal Reflector with Natural Metal Ring

NS-53 = 4" Copper Reflector with Copper Metal Ring

Compatible Housings

Line Voltage

Catalog No.

NFBIC-4INCATA = 2-Hour Fire Rated New Construction / 35W max.
NS-4010AT = Non-IC Air-Tight New Construction / 50W max.
NS-4010AT/IC = IC Air-Tight New Construction / 15W max.
NSIC-4010AT = IC Air-Tight New Construction / 50W max.
NSR-4040AT = Non-IC Air-Tight Remodel / 50W max.
NSRIC-4040AT = IC Air-Tight Remodel / 50W max.

GU24

Catalog No.

NHIC-4G24AT = 4" IC Air-Tight GU24 New Construction / 26W max

Example: NS-44HZ = 4" Haze Reflector with White Metal Ring

