



Phlebotomy Cart

Our Phlebotomy Cart comes with all the amenities of a much more expensive competitor. It is height adjustable (from 36" to 46"). It has a large drawer for supplies. The drawer is available with a flat key lock, thumb latch or electronic lock. The innovative surface smoothly slides back to expose the contents of the drawer. The cart also includes a single glove box holder as well as adjustable brackets to hold numerous sized sharps containers (sharps container not included). The surface and drawer are fabricated from 1/8" painted aluminum. The painted aluminum will withstand years of abuse and disinfectants.

- Outside dimensions of work surface 15 9/16" W x 17" D x 1" H
- Inside dimensions of work surface 15 5/16" W x 15 3/8" D
- Height of work surface adjusts from 36" to 46"
- Includes a 183035 Large Med Drawer 13 7/8" W x 15 3/8" D x 6 3/4" H
- Built-in handle on back and front of unit for easy transport
- 350340 is sold with a flat key lock with 3 keys. Multiple units will be keyed with the same lock number
- 350340D is sold with a flat key lock with 3 keys. Multiple units will be keyed with different lock numbers
- 350340T is sold with a non-locking thumb latch.
- Includes Single wire glove box holder & Adjustable straps to hold most sharps containers
- Sturdy 5 leg base with 3" casters

Additional lock features for the 350341

- 1 Master Code
- 19 User Codes
- Code Length 4-8 digits
- 75,000 Cycles per battery replacement
- Low battery replacement indicator
- Batteries can be replaced without opening the drawer
- 1 Year Warranty

Additional Lock Features for the 350341AT (Audit Trail) –

- Includes all features for the 350341
- Allows administrator to view the last 1500 accesses
- No Software required (uses ActiveTrack down-loadable Excel Spreadsheet)
- Connect lock to laptop using USB A to micro USB (not included)