

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_



# P1841-ICAT

5" Shallow Incandescent Recessed Housing. Both IC and Non-IC rated. Air-tight. Socket mounts to trim for optimum performance and consistent lamp position and can use a variety Incandescent, CFL and LED lamps. Housing is suitable for residential or light commercial applications. For installation in insulated ceilings and non-insulated ceilings with airtight code compliant construction. The housing can be used with a variety of trims and finishes to create different lighting effects or to match any decor. The trims uses friction springs to attach to the housing to provide a flush fit against the ceiling.

**Width: 6"**  
**Length: 12-1/8"**  
**Height: 5-3/8"**

- Universal J-box with snap-out sides
- Removable housing for field inspection of wiring
- Ceiling opening measures 5-5/8 in
- Recessed depth measures 5-1/2 in
- Pry outs 1/2 in and 3/4 in

**Category:** Recessed-Housing

**Finish:** Unfinished

**Construction:** Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Recessed mounted	Pre-wired 120 V	Quantity: E26 base	cULus 1 year warranty