

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_



## P1841-LED

5" LED Recessed Housing. IC rated and Air-Tight. Features an integral quick link connector for use with LED integrated trims or modules. Airtight rating reduces airflow between living spaces and unconditioned areas providing additional energy savings. Housing is suitable for residential or light commercial applications.

**Width: 6"**  
**Length: 12-1/8"**  
**Height: 5-3/8"**

- Universal J-box with snap-out sides
- Removable housing for field inspection of wiring
- Ceiling opening measures 5-5/8 in
- Recessed depth measures 5-1/2 in
- Pryouts 1/2 in and 3/4 in

**Category:** Recessed-Housing

**Finish:** Unfinished

**Construction:** Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Recessed mounted	Pre-wired 120 V	Quantity:	cCSAus 1 year warranty