

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300274-009 Winslett

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this bath light from the Winslett Collection. Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines coated in a beautiful brushed nickel finish. Lightly seeded glass shades rest in shiny pedestal light bases that add an unexpected, but welcomed dash of modern personality to this clean, traditional design.

- Lightly seeded glass shades rest in shiny pedestal light bases that add an unexpected, but welcomed dash of modern personality to this clean, traditional design.
- Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines coated in a beautiful brushed nickel finish.
- Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this bath light.
- Ideal for any bathroom.
- Perfect for transitional, rustic, farmhouse, and coastal settings.
- Measures 23-3/4-inch width by 7-1/4-inch height.
- Uses three medium base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Clear Seeded glass Cylindrical Shade



Width: 23-3/4 in
Height: 7-1/4 in
Depth: 7-3/8 in
H/CTR: 4-1/4 in (glass facing up)

Clear Seeded glass Cylindrical Shade
Width: 4-3/4 in
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Three 60 W max. Medium Base or LED equivalent	CULus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	E26 base Porcelain sockets	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V		
Canopy covers a standard 4" recessed outlet box: 7.125" W., 4.5" ht., 0.75" depth			