

## Description:

Harkening back to a simpler time, the Inspire Collection freshens traditional forms with flowing lines. The LED semi-flush fixture features an etched glass diffuser with a summer linen shade finished with Graphite details. This fixture is suitable for a variety of design styles, including Modern, Traditional and Farmhouse and the simple design is a perfect complement to a variety of fixture collections.

## Specifications:

- Graphite (-143) (painted)
- Steel Construction
- Summer Linen fabric Shade, Etched glass diffuser
- LED Module is replaceable (part # 93074038)
- Gives a dash of flair to the standard ceiling light
- Fits seamlessly within Modern, Traditional and Farmhouse interiors
- Dramatic Graphite finish
- Measured 13in diameter x 10 1/8in ht.
- Contains one 17W LED Module
- 1,452 lumens 83 lumens/watt (source), 3000K color temperature, 90+ CRI
- CSA Safety listed for use in damp locations
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

## Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1452/83 (LM-82)
Lumens/LPW (Delivered)	939/51.6 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	-30°C
Warranty	5 year limited warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

## P350134-143-30

## Images:



## Dimensions:

Diameter: 13"  
Height: 10-5/8"

Glass  
Width: 12-5/8"  
Height: 0-1/8"  
Glass 2  
Width: 4-1/2"  
Length: 13"  
Height: 13"

## P350134-143-30

### Dimming Notes:

---

P350134 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.