

Parallel LED

Wall Mounted • Damp Location Listed PROGRESS LED

Description:

Parallel LED vanity and sconces feature a tubular opal glass diffuser paired with a simple, modern metal canopy. An integrated LED source provides a variety of energy and cost savings benefits. Suitable for residential and commercial applications. Polished Chrome finish.

Specifications:

- Etched White glass Cylindrical
- A cylindrical design pairs with an oval back plate to create a harmonious design
- 11" linear 16-watt LED wall bracket
- Etched white glass
- Polished Chrome finish
- Integrated LED source provides a variety of energy and cost savings benefits for the homeowner
- Measures 4 3/4" W x 7 1/2" H
- 918 lumens 56 lumens/watt (delivered)
- Warm white 3000K lighting color and 90+CRI
- Modern style and continuous illumination are ideal for a variety of bath and vanity settings - including Mid-Century and Luxe
- Steel construction
- ADA compliant
- Dimmable with most Triac or ELV type dimmers
- California Title 24 compliant
- Damp location listed
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" recessed outlet box: 4.75 in W., 7 in ht., 0.625 in depth
- Mounting plate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	16 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	918/56.7 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed Meets California Title 24 JA8-2016


P710050-015-30



Dimensions:

Width: 4-3/4 in
Height: 11 in
Depth: 2-3/4 in
H/CTR: 7-1/2 in

Etched White glass Cylindrical
Width: 1-15/16 in
Height: 9-15/16 in



P710050-015-30

Dimming Notes:

P710050-015-30 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron - NTELV-300

Lutron - DVELV-300P

Lutron - DVCL-253P

Lutron - Caseta Wireless

Leviton - 6672

Leviton - 6674

Leviton - 6681

Lutron - AYCL-153P

Lutron - TGCL-153PH

Lutron - AYLV-600P

Lutron - NTLV-600

Lutron - MAELV-601

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.