

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P710087-009 Hartwick

Ease yourself into a state of complete bliss and relaxation under the luxurious glow of this wall sconce. A stunning, cylinder-shaped etched opal glass diffuser held in place by a thin metal bar recalls visions of elegant candlesticks. The diffuser sits on top of a pedestal-like light base attached to a beautiful brushed nickel backplate.

- A stunning, cylinder-shaped etched opal glass diffuser held in place by a thin metal bar recalls visions of elegant candlesticks.
- The diffuser sits on top of a pedestal-like light base attached to a beautiful brushed nickel backplate.
- Ease yourself into a state of complete bliss and relaxation under the luxurious glow of this wall sconce.
- Ideal for any bedroom, living room, sitting room, hallway, foyer, or bathroom.
- Perfect for modern, contemporary, and luxury settings.
- Measures 4-1/2-inch width by 13-1/2-inch height.
- Uses one medium base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Wall Brackets

**Finish:** Brushed Nickel (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Etched Opal glass Cylindrical Shade



Width: 4-1/2 in  
Height: 13-1/2 in  
Depth: 4 in  
H/CTR: 9-1/8 in

Etched Opal glass Cylindrical Shade  
Width: 2-7/8 in  
Height: 9-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CULus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	One 60 W max. Medium Base or LED equivalent	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 13.5" ht., 0.625" depth	120 V	E26 base Porcelain socket	Americans With Disabilities Act (ADA) compliant