



### STANDARDS

ANSI 107-2020 • TYPE 0 CLASS 1

Waterproof — ANSI 107-2020: AATCC 127

Waterproof polyester shell with quilted lining // Zipper front closure // Concealed drawstring hood // 2" silver reflective striping with contrasting color trim // Elastic band at waist and wrists // Mic tabs and pencil pocket // Cell phone/radio chest pocket with clear panel

RJ3711 •

S-6XL

POCKETS
4 OUTER, 1 INNER





#### **STANDARDS**

ANSI 107-2020 TYPE 0 CLASS 1 Not FR Waterproof — ANSI 107-2020: AATCC 127

# **SPECS**

#### MATERIALS

Jacket 300D polyurethane (PU) coated waterproof polyester shell

Interior 180gsm quilted polyester cotton

Inner Lining 210T taffeta Reflective Tape Generic silver

Waist & Wrists Waterproof elastic band

CLOSURE

Front SBS Zipper

Zipper Tape 100% polyester fabric

Zipper Teeth Resin
Zipper Slider Metal
Hood Drawstring

#### REFLECTIVE STRIPING

One 4" stripe of contrasting material with 2" silver reflective stripe centered inside applied horizontally across lower chest dividing black material from lime material

Two 4" stripes of contrasting material with 2" silver reflective stripes centered inside applied vertically from top of horizontal stripe, over shoulders, to top of horizontal stripe on back

Two 4" stripes of contrasting material with 2" silver reflective stripes centered inside applied around each sleeve

## POCKETS

Two outer lower slash zipper pockets: 9" x 9"

One outer left chest clear badge hook and loop pocket with clear ID holder:  $3.5" \times 5.9"$ 

One outer left arm pencil pocket: 3" x 5"

One inner left chest hook and loop pocket:  $6" \times 7"$ 

#### **JACKET MEASUREMENTS**

	S	М	L	ХL	2 X	3 X	4 X	5 X	6 X
Chest Measurements	26"	27"	28"	29"	30"	31"	33"	34.5"	36"

Jacket measurements are taken while garment is lying flat. Please note: some size variation may occur.

#### **WASHING INSTRUCTIONS**



Machine wash cold



Do not bleach



Tumble dry, low heat



Do not iron



Do not dry clean

Max 25 washes

