



PYRAMEX



RPB36 Series



STANDARDS

ANSI 107-2020 • TYPE R CLASS 3

Waterproof — ANSI 107-2020: AATCC 127

OUTER PARKA

Teflon treated™ // Waterproof rip-stop polyester shell with quilted lining // Dual zipper front closure with hook and loop storm flap // 2" non-connected silver reflective striping // Concealed detachable hood with drawstring slack adjustment // Elastic band at wrists // Interior access zipper for print customization // Badge lanyard, d-ring accessory hook, and 2 mic tabs

● RPB36.10 •

M-5XL

INNER JACKET

Polyester fleece // 2" non-connected silver reflective striping // Elastic band at wrists // Drawstring around bottom

POCKETS

OUTER PARKA: 8 OUTER, 2 INNER

INNER JACKET: 2 OUTER, 2 INNER

PYRAMEX®



P 800.736.8673 // F 901.861.4967 // W PYRAMEX.COM



PYRAMEX

STANDARDS

ANSI 107-2020 TYPE R CLASS 3 Not FR

Waterproof — ANSI 107-2020: AATCC 127

SPECS

MATERIALS

Outer Parka	300D polyurethane (PU) coated waterproof polyester shell Teflon™ treatment
Interior	140gsm quilted polyester cotton 210T taffeta
Inner Jacket	100% polyester 250gsm fleece
Reflective Tape	Generic silver
Wrists	Waterproof elastic band (outer parka)

CLOSURE

Front	SBS Zipper
Zipper Tape	100% polyester fabric
Zipper Teeth	Resin
Zipper Slider	Metal

REFLECTIVE STRIPING

Outer Parka

- Two 2" non-connected silver reflective stripes applied horizontally across lower chest
- Two 2" non-connected silver reflective stripes applied vertically from top of horizontal stripe, over shoulders, to top of horizontal stripe on back
- Two 2" silver reflective stripes applied around each sleeve

Inner Jacket

- One 2" non-connected silver reflective stripe applied horizontally across lower chest
- Two 2" non-connected silver reflective stripes applied vertically from top of horizontal stripe, over shoulders, to top of horizontal stripe on back
- Two 2" silver reflective stripes applied around each sleeve

POCKETS

Outer Parka

- Two outer lower slash pockets with zipper closure: 9" x 9"
- Two outer lower flap pockets with hook and loop closure: 9" x 9"
- Two outer chest slash pockets with zipper closure: 12.5" x 10.5" *
- One outer storm flap zipper pocket: 9.5"
- One outer left arm split pencil pocket: 3" x 5"
- One inner left chest split pencil pocket: 6.5" x 7"
- One inner right chest pocket: 5.9" x 7.8"

Inner Jacket

- Two outer lower slash pockets with zipper closure: 9" x 9"
- Two inner lower pockets: 9" x 9"

* Measurement varies with size of garment. Measurement shown based on size XL.

OUTER PARKA MEASUREMENTS

	M	L	XL	2X	3X	4X	5X
Chest Measurements	27"	28.5"	30"	31"	32.5"	34"	35.5"

Parka measurements are taken while garment is lying flat.
Please note: some size variation may occur.

INNER JACKET MEASUREMENTS

	M	L	XL	2X	3X	4X	5X
Chest Measurements	24"	25.5"	27"	28"	30"	31"	32"

Jacket measurements are taken while garment is lying flat.
Please note: some size variation may occur.

WASHING INSTRUCTIONS



Machine wash cold



Do not bleach



Tumble dry, low heat



Do not iron



Do not dry clean

Max 25 washes

