



RPB38 Series



STANDARDS

ANSI 107-2020 • TYPE R CLASS 3

Waterproof — ANSI 107-2020: AATCC 127

OUTER PARKA

Teflon treated™ // Waterproof fluorescent background rip-stop polyester shell // Dual zipper front closure with hook and loop storm flap // 2" non-connected silver reflective striping // Concealed detachable hood with drawstring and slack adjustment // Elastic band at wrists // Interior access zipper for print customization // Badge lanyard with D-ring accessory hook and 2 mic tabs

● RPB38.10 •

S-5XL

INNER JACKET

Polyester fleece // 2" non-connected silver reflective striping // Elastic band at wrists // Drawstring around bottom

POCKETS

OUTER PARKA: 8 OUTER, 2 INNER
INNER JACKET: 2 OUTER, 2 INNER



PYRAMEX

STANDARDS

ANSI 107-2020 TYPE R CLASS 3 Not FR

Waterproof — ANSI 107-2020: AATCC 127

SPECS

MATERIALS

Outer Parka 300D polyurethane (PU) coated waterproof polyester shell
Teflon™ treatment

Interior 210T taffeta

Inner Jacket 100% polyester
250gsm fleece

Reflective Tape Generic silver

Wrists Waterproof elastic band (outer parka)

CLOSURE

Front SBS zipper

Zipper Tape 100% polyester fabric

Zipper Teeth Resin

Zipper Slider Metal

REFLECTIVE STRIPING

Outer Parka

Two 2" non-connected silver reflective stripes applied horizontally across lower chest

Two 2" non-connected silver reflective stripes applied vertically from top of horizontal stripe, over shoulders, to top of horizontal stripe on back

Two 2" silver reflective stripes applied around each sleeve

Inner Jacket

One 2" non-connected silver reflective stripe applied horizontally across lower chest

Two 2" non-connected silver reflective stripes applied vertically from top of horizontal stripe, over shoulders, to top of horizontal stripe on back

Two 2" silver reflective stripes applied around each sleeve

POCKETS

Outer Parka

Two outer lower slash pockets with zipper closure: 9" x 9"

Two outer lower flap pockets with hook and loop closure: 9" x 9"

Two outer chest slash pockets with zipper closure: 12.5" x 10.5"*

One outer storm flap zipper pocket: 9.5"

One outer left arm split pencil pocket: 3" x 5"

One inner left chest split pencil pocket: 6.5" x 7"

One inner right chest pocket: 5.9" x 7.8"

Inner Jacket

Two outer lower slash pockets with zipper closure: 9" x 9"

Two inner lower pockets: 9" x 9"

* Measurement varies with size of garment. Measurement shown based on size XL.

OUTER PARKA MEASUREMENTS

	S	M	L	XL	2X	3X	4X	5X
Chest Measurements	26"	27"	28.5"	30"	31"	32.5"	34"	35.5"

Parka measurements are taken while garment is lying flat.
Please note: some size variation may occur.

INNER JACKET MEASUREMENTS

	S	M	L	XL	2X	3X	4X	5X
Chest Measurements	23"	24"	25.5"	27"	28"	30"	31"	32"

Jacket measurements are taken while garment is lying flat.
Please note: some size variation may occur.

WASHING INSTRUCTIONS



Machine wash cold



Do not bleach



Tumble dry, low heat



Do not iron



Do not dry clean

Max 25 washes

