

LiftPac®

Flexible UN Rated
Disposal Bag

PACTEC

LIFTPAC®

800.272.2832

www.pactecinc.com

INSTRUCTIONS:

1. Stand unit upright
2. Fold out sides until square
3. Load until full, then zip closed



13H4/X/0416

IND/100850394/2600/1383

PACTEC

We manufacture packaging.
We engineer solutions.

LiftPac®

Flexible UN Rated Disposal Bag



PacTec's LiftPac® is the only self-standing zipper-top hazardous waste bag on the market. This cubic yard bag is the perfect solution for the disposal of household hazardous waste, contaminated PPE, and a variety of other applications.

The LiftPac® walls are constructed of rigid corrugated fiberboard allowing the bag to be self-standing, while the glued-in 6 mil PE liner provides ultimate leak protection. It contains the equivalent of four 55-gallon drums and can hold over 3,000 pounds at a significant savings in cost and storage space. They are lightweight, easy to assemble, versatile, and can easily be lifted by forklift with attached loops.

Applications:

- ▶ Household Hazardous Waste
- ▶ Lab Packing
- ▶ Contaminated PPE
- ▶ Asbestos & Other Dusts
- ▶ Wastewater Treatment Sludges
- ▶ Contaminated Soil (wet or dry)

Features:

- ▶ UN-Rated "X" for Packaging Groups I, II and III
- ▶ Cardboard sidewall supports hold bag open for easy filling
- ▶ Patented zipper closure
- ▶ UV Coated, weather resistant outer layer

Advantages:

- ▶ Self-contained multi-layer unit
- ▶ Superior to stapling boxes to pallets
- ▶ Lightweight and compact at 3'x3'x3'
- ▶ Lowers disposal costs as compared to 55-gallon drums
- ▶ Collapsible for easy storage

Quality Assurance is a top priority for PacTec.

Our reputation is built on it. Our certifications confirm it.

PacTec maintains a formal quality management system that meets the requirements of ISO 9001:2015 and NQA-1.

Innovative design, customized solutions and rigorous testing are a part of everything we do at PacTec.

We manufacture packaging. We engineer solutions.

**Exceeding Expectations,
One Customer at a Time . . .**



PACTEC

1-800-272-2832
www.pactecinc.com