

Part Number: PSCH6B

Product Description: ONE-PIECE STRUT CLAMP WITH SADDLE USED TO SECURE 3/8" CONDUIT



Material Specifications

Type: Zinc Plated Steel

Finish: Zinc

Color: Silver

Function Specifications

Compatible Wires and Cables

AC/MC CABLE (OD):
Drop Wire:
Plain Rod (in):

Threaded Rods and Bolts

Tapped Holes:
Clearance Holes (in):
Threaded Rod Size (in):

Compatible Conduit

EMT Size (in): 3/8
Rigid/IMC (in):

Compatible Flanges and Studs

Flange Size (in):
Metal Stud Size (ins):

Static Load Rating

Vertical (lbs):
Horizontal (lbs):

Other

Clamps with Saddle, suitable for use with standard 1-5/8 strut

Codes and Regulatory

Regulatory Certifications: UL/cUL

Country of Origin: CN

Packaging

General Packaging: Cardboard Box
Box Size: 8.25 X 6.25 X 6

Pieces per Package: 100
Other Box Features:

Document Information

Created By: DBLA
Checked By: DJW
Approved By: KLN

Customer Specification #: C11384
Revision Level: 01
ECN #: GAECN01482
Date: 12/10/2013