



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	MATERIAL (COLOR)	NAIL PART NO.	"A" NAIL LENGTH FROM FLANGE (REF)	"B" NAIL DIA. (REF)	"C" HOL DIA. (REF)	"D" OVERALL HEIGHT (REF)
QB-FN1-Q	ABS (WHITE)	HBN1-T	1.0 [25.4]	.074 [1.880]	.079 [2.007]	2.17 [55.12]
QB-FN2-Q	ABS (BLACK)	HBN2-T	2.0 [50.8]	.094 [2.388]	.094 [2.388]	3.17 [80.52]
QB-FN3-Q	ABS (GRAY)	HBN3-T	3.0 [76.2]	.121 [3.073]	.128 [3.251]	4.17 [105.92]

NOTES:

1. DIMENSIONS IN BRACKETS [] ARE METRIC [mm]
2. PRODUCT DESIGNED TO BE INSERTED INTO PANDUIT PART: QB-MOUNT
3. PRODUCT DESIGNED TO SUPPORT A MAXIMUM STATIC LOAD OF 5 LBS WITH COMPATIBLE PARTS.
4. PRODUCT IS RATED FOR ENVIRONMENTAL CONDITIONS OF 40-100°F IN ALL HUMIDITY RANGES.
5. PRODUCT DESIGNED TO SUPPORT ANY COMBINATION OR ARRANGEMENT OF 1 TO 5 NAILS.
6. NAILS SOLD SEPARATELY.



TITLE		QUICK-BUILD FIVE NAIL BASE FOR USE WITH HBN1-T, HBN2-T, HBN3-T; 25 PER PACKAGE. (QB-FN1-Q, QB-FN2-Q, QB-FN3-Q)	
CUSTOMER DRAWING			
ITEM REVISION NAME	14L203AP/01	PANDUIT	
DATASET FILE NAME	14L203AP_DC/00		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [2.54] .xxx ± .005 [.127]		SEE NOTES	
.xx ± .01 [.25] ANGLES ± 5 °		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		14L203AP-DC	
DRAWN BY	DATE	CHK	SCALE
ANF	06-15-15	DJW	1:2
REV	DATE	BY	DESCRIPTION
00	06-15-15	ANF	DJW
MSAD	DRAWING RELEASE		GAECN03013
APR	DESCRIPTION		ECN
SHT 1 OF 1		SIZE	
A		A	