


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PLT1M	.06 (1.5)	.87 (22)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	18 (80)	MINIATURE	.07 (32)
PLT2I	.06 (1.5)	2.00 (51)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	8.0 (203)	40 (178)	INTERMEDIATE	.20 (91)
PLT2S	.06 (1.5)	1.88 (48)	.052 (1.3)	.190 (4.8)	.258 (6.6)	.220 (5.6)	.316 (8.0)	7.4 (188)	50 (222)	STANDARD	.29 (132)
PLT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	50 (222)	STANDARD	.45 (204)

NOTES:

- * 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE. SEE NOTE 2 FOR PART NUMBER SUFFIX FOR PART COLOR.
- 2. CABLE TIES ARE AVAILABLE IN 4 DIFFERENT FLUORESCENT COLORS:

PART NUMBER SUFFIX	COLOR
-53	ORANGE
-54	YELLOW
-55	GREEN
-59	PINK

REV						DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE			
06	9/13/13	BWG	KJM	RTFI	UPDATED TOLERANCES & TITLE BORDER. SEE ECN FOR COMPLETE DETAILS	SS-26476/06					PAN-TY FLUORESCENT LOCKING CABLE TIE CUSTOMER DRAWING ITEM REVISION NAME: 108015KO/00 DATASET FILE NAME: 108015KO/00 SS_26476_REV06 UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x : .005 .xxx : .020 (.51) .xx : .02 (.5) ANGLES : .005 THIRD ANGLE PROJECTION				
												MATERIAL: NYLON 6.6 DRAWING NUMBER: SS-26476 SCALE: NONE SHT 1 OF 1 SIZE: A			

D:\101000A\16