

HDMI to DVI Cable, Digital Monitor Adapter Video Converter Cable (HDMI to DVI-D M/M), 6 ft. (1.83 m)

MODEL NUMBER: P566-006



Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and DVI-enabled display.

Description

Tripp Lite's 6-ft. (1.83 m) HDMI - DVI (High Definition Multimedia Interface) cable allows interconnection between digital display devices, such as DTV's (Digital Television), Plasma displays, LCD TV's, and projectors, to Digital source devices, such as Digital Set-Top boxes, DVD/DVD-R players, and AV receivers. HDMI DTV's will display video received from existing DVI-equipped products, and DVI-equipped TVs will display video from HDMI sources. The DVI-HDMI adapter does not support audio and supports digital video only.

Features

- 6-ft. (1.83 m) HDMI to DVI-D Single Link Adapter Cable
- Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and a DVI-enabled display.
- Gold plated connectors and contacts provide optimal signal transfer
- Premium Double-Shielded HDMI compliant cable protects against outside noise (EMI/RFI)
- Impedance matched twisted pair construction reduces cross-talk and interference
- Supports High-Definition (HD) video resolutions up to 1920 x 1080 @60Hz (1080p).

Specifications

OVERVIEW	
UPC Code	037332122919
Technology	DVI; HDMI

Highlights

- Premium double shielded digital video cable protects against EMI/RFI noise.
- Gold plated connectors and contacts provide optimal signal transfer.
- Supports high-def video resolutions up to 1920 x 1080 @60Hz (1080p).
- Supports a bandwidth up to 5Gbps
- This product is covered by a Lifetime Limited Warranty

Package Includes

- 6-ft. (1.83 m) HDMI to DVI Gold Digital Video Cable - HDMI-M/DVI-M



VIDEO	
Max Supported Video Resolution	1920 x 1080 @60Hz (1080p)
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	5.5mm
Cable Jacket Rating	VW-1
Wire Gauge (AWG)	30AWG
Cable Length (ft.)	6
Cable Length (m)	1.8
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.24
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 113°F (0 to 45°C)
Storage Temperature Range	14 to 158°F (-10 to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
Connector Plating	Gold
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
HDCP Specification	1.3
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>