



## IKBC384S

### Under Cabinet

Stream music from your device to the IKBC384S for unrivaled control of your listening experience. Enjoy your CD's and listen to music, news, weather, and traffic with the FM radio. The IKBC384S also features a kitchen timer, and a simple mounting kit for easy installation.

#### FEATURES

- Supports Bluetooth v2.0
- Supports profile A2DP (Advanced Audio Distribution Profile)
- Supports automatic device pairing
- Wireless range: 33 feet
- CD player: CD, CD-R/RW
- Digital FM radio (PLL)
- Station memory presets (20 FM)
- Negative LCD display with white backlight
- Timer
- Digital clock
- Pairing button
- Play/pause button
- Disc playback: random, repeat, program
- Digital volume control
- Drawer-load disc player
- Built-in FM wire antenna
- Built-in speakers
- 3.5mm audio input
- Last user's setting memory
- Remote
- DC power input: requires an AC/DC power adapter (included)
- Battery backup: requires 2 AAA batteries (not included)

#### INCLUDES

- Remote control: requires a CR2025 battery (pre-installed)
- Mounting hardware
- AC/DC power adapter
- Warranty
- User's guide

Production  
976-21

#### MASTER CARTON

DIM(LxWxH): 13.78 x 8.11 x 14  
CuFt: 0.91  
Weight: 8.24  
Qty: 2  
MC UCC-14: 50-047323-003849

#### INNER CARTON

DIM(LxWxH): x x  
CuFt:  
Weight:  
Qty:  
UCC-14:

#### GIFT BOX

DIM(LxWxH): 13.39 x 3.78 x 12.44  
Weight: 3.7

#### GIFT PACK

Pkg: 4 Color Gift Box  
UPC: 047323-003844

#### ITEM

DIM(LxWxH): 11.42 x 11.54 x 2.87  
Weight: 2.86

#### GENERAL

Color: Silver  
Duty: 0  
HTS: 8527.91.6040  
MOQ: 3960  
FOB: Yantian

#### WAREHOUSE

Ctn/Layer:  
Layers/Skid:  
Ctns/Skid: 0  
Units/Skid: 0  
Skids/Truck(48Ft): 28  
Skids/Truck(53Ft): 30  
Units/Truck(48Ft): 0  
Units/Truck(53Ft): 0  
Skid Size: 48 x 40 x

#### CONTAINER

20' Cont Qty: \*2304  
40' Std. Qty: 3960  
40' HQ Qty: \*5295  
45' Cont Qty: \*5986

#### CONTENTS

Electronics: 40 Glass:  
Plastics: 57 Wood:  
Metal: 3 Other: