



## PipeMan 24" Pipe OD Tape Measure

- Measures up to 24" Pipe
- Side One Top: 61 Metric
- Side One Bottom: 78" Inches
- Side Two: Top: OD by 100ths
- Side Two Bottom: 200cm
- Part No: 416-04-024

(aka Pipe OD Tape, Diameter Tape, Outside Diameter Tape, Pi Style OD Tape)



<p><b>Inches</b></p> <p><b>Metric</b></p> <p><b>1/100th's (OD)</b></p> <p><b>&amp; Centimeters</b></p> <p><b>aka OD Tape,</b></p> <p><b>Diameter Tape,</b></p> <p><b>and, or Pi Style Tape</b></p>	<p><b>Specifications:</b></p> <ul style="list-style-type: none"> <li>• Heavy Duty Flexible tape</li> <li>• Locking Function</li> <li>• Auto Retraction Function</li> <li>• 78" Standard Tape Measure (side 1 top)</li> <li>• 200cm Metric Tape Measure (side 1 bottom)</li> <li>• 61 Metric OD Tape Measure (side 2 top)</li> <li>• 24" Pipe OD Tape Measure in 1/100th inch (side 2 bottom)</li> <li>• Key Chain Design</li> </ul>
--	---

***We can personalize these 24" OD Tape Measures for your company  
Best Prices! – Minimum 1,000 units for personalization***