



**POINT  
LIGHTING**  
CORPORATION

# POINT LIGHT BASE PLS SHALLOW MOUNTING BASE

The PLS-40304 shallow light base is installed below grade to mount the 8-inch diameter PRL LED inset light and, with the PL40301 baseplate, to mount elevated lights. The PLS is intended to be set in concrete. The PL10049-4-6 flat gasket is used in all cases. The PLS base is cast aluminum powder coated for corrosion resistance. Option -PLS for elevated lights includes the base, gasket and the PL40301 baseplate. The PLS is standard with two 1-inch NPT hubs at 0 & 180 degrees. It is shipped with a temporary plywood cover and stainless steel bolts. The blank coverplate PL40302-X is available. Option -GR ground lug may be internal or external.

| Point Type | Hubs*      | (Locations)*   | Hub Size*                | Options                                       |
|------------|------------|----------------|--------------------------|---|
| PLS-40304  | 1, 2, 3, 4 | (0,90,180,270) | 34: ¾-inch<br>10: 1-inch | GR: Ground Lug #4-14<br>DH: Drain Hole ¾-inch |

\* If no sizes & locations are specified, bases are assumed to be two (2) 1-inch NPT hubs at 0 & 180-deg

Example: PLS-40304-2(0,90)-10-GR Base with two 1-inch hubs at 0 & 90-deg and ground lug

As required, blank metal coverplate with gasket & hardware: PL10777-X\* \* -16 for PRL & -8 for PEL/PHL

FOR PRL LED INSET LIGHTS:  
IF THE BASES ARE INSTALLED LOWER  
THAN INSTRUCTED, SPACER RINGS  
WILL BE REQUIRED: PL10701-X  
X = EIGHTHS OF AN INCH

BASEPLATE & BASE 8-IN DIAMETER  
WITH SIX (6) MOUNTING HOLES  
SPACED EQUALLY AT 120 DEGREES  
ON A 7-IN DIAMETER BOLT CIRCLE

