

# P - 01 Hook

## Art. No. P01H-x



Toolflex P-01 hook for P-01 rail.

Pack of 3.

Hygienic design with click 'n go function.

The system is extendable so it is easy to add additional rails and simple to click on additional hooks or attachments.

Available in 8 different colors:

- Orange
- Black
- Red
- White
- Blue
- Green
- Yellow
- Purple

#### Food contact compliance (raw materials)

Regulation (EC) No 1935/2004	Yes
Regulation (EC) No 10/2011	Yes
US FDA 21 CFR	Yes
AP 89 (1)	Yes

#### Technical Data

Materials	POM
Box Quantity	20 pcs
Maximum cleaning temperature (Dishwasher)	93°C
Maximum cleaning temperature (Autoclave)	121°C
Minimum temperature	- 20°C
Maximum temperature	80°C
Maximum weight individual hook	3 kg
Gross Weight	0,875 kg
Net Weight	0,037 kg
Country of Origin	Sweden
Custom tariff code	39 26 90 98 00