

Rail 54-3

Art. No. 5-3-x



Toolflex 54 cm rail with 3 x P-01 holders, including screws.

Hygienic design with click 'n go function makes it simple to remove individual holders, or the complete rail.

The new wall bracket improves the ability to clean behind the rail and reduces the risk of contamination.

Available in 8 different colours:

- Orange
- Black
- Red
- White
- Blue
- Green
- Yellow
- Purple

<u>Pallet type</u>	<u>Pallet</u>	<u>20ft container</u>	<u>40ft container</u>	<u>Units / Layer</u>	<u>Layer / Pallet</u>
120x80 cm	320 pcs	3200 pcs	6720 pcs	8 pcs	40 pcs
<u>Pallet type</u>	<u>Pallet</u>	<u>20ft container</u>	<u>40ft container</u>	<u>Units / Layer</u>	<u>Layer / Pallet</u>
120x100 cm	400 pcs	4000 pcs	8400 pcs	10 pcs	40 pcs

Food contact compliance (raw materials)

Regulation (EC) No 1935/2004	Yes
Regulation (EC) No 10/2011	Yes
US FDA 21 CFR	Yes
AP 89 (1)	Yes

Technical Data

Hold tools from	Ø 15 - 35 mm
Materials	POM, PP, TPE, Aluminium
Box Quantity	1 pcs
Maximum cleaning temperature (Dishwasher)	93°C
Maximum cleaning temperature (Autoclave)	121°C
Minimum temperature	-20°C
Maximum temperature	80°C
Maximum weight individual holder	5 kg
Maximum weight rail	25 kg
Gross Weight	0,61 kg
Net Weight	0,36 kg
Country of Origin	Sweden
Custom tariff code	39 25 90 10 00