

C1220D C1220D-PD

Ceiling Fixture & Pendant

Features

Housing

Die-formed Cold-rolled Steel

Finish Option: -08 Gray, -30 Oil Rubbed Bronze, -05 Black

Pendant Mount by Hanging cable

Optical

Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity

LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light

Electrical

High Power Factor, Low THD

Bi-Level Lighting and Emergency Backup Model Available

Lamp

LED Type: Built-in (Color Temperature Option – 3000K, 4000K)

Multiple Color Temperature (MCT, 3000K/35000K/4000K) Option Available

Certifications

ETL/cETL Listed

Warranty

5 Years Warranty on Driver and LED Module



LED Type

Model	Input Voltage	Input Wattage	CRI	Lumen (Typ) / CT	Finish	Shade	Dimension (OD X H)
C1220D-30-xxxxK	120V ~ 277V	58W	> 80	3100 / 3000K or 4000K	Oil Rubbed Bronze	Acrylic	19.7" x 4.2"

Pendant / LED Type

Model	Input Voltage	Input Wattage	CRI	Lumen (Typ) / CT	Finish	Shade	Dimension (OD X H1 x H)
C1220D-PD-30-xxxxK	120V ~ 277V	58W	> 80	3100 / 3000K or 4000K	Oil Rubbed Bronze	Acrylic	19.7" x 4.2" x 6.0'

H: Hanging Cable