

# FL5524D-J-MCT FL5539D-J-MCT FL5554D-J-MCT

## LED Vanity

### Features

#### Housing

Die-formed Cold-rolled Steel

Finish Option: - 30 Oil Rubbed Bronze, - 62 Satin Nickel, -05 Black, -06 White, -09 Silver

#### Optical

Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity

LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light.

#### Electrical

High Power Factor, Low THD

#### Lamp

LED Module: Multiple Color Temperature Type (MCT, Adjustable, 3000K/3500K/4000K)

#### Certification

ETL/cETL Listed, Damp Rated, CEC Listed (Title 24)

#### Warranty

5 Years Warranty on Driver and LED Module



### LED Type

| Model            | Input Voltage | Input Wattage | LED CT            | Lumen (TYP) | Finish       | Shade   | Dimension (L X H X E) | CEC Listed |
|------------------|---------------|---------------|-------------------|-------------|--------------|---------|-----------------------|------------|
| FL5524D-J-MCT-62 | 120V – 277V   | 17W           | 3000K/3500/ 4000K | 1530        | Satin Nickel | Acrylic | 22.0" x 4.7" x 2.7"   | Yes        |
| FL5539D-J-MCT-62 | 120V – 277V   | 23W           | 3000K/3500/ 4000K | 2600        | Satin Nickel | Acrylic | 34.0" x 4.7" x 2.7"   | ---        |
| FL5554D-J-MCT-62 | 120V – 277V   | 35W           | 3000/ 3500K/4000K | 3500        | Satin Nickel | Acrylic | 46.0" x 4.7" x 2.7"   | ---        |