

# P607D

## LED Pendant

### Features

#### Housing

Die-formed Cold-rolled Steel

Shade: Clear Glass Create Excellent Light Distribution and Uniformity

Canopy Size: 4.8" OD x 1.0" H

#### Electrical

120V

#### Lamp

LED Bulb: E26, ST21, 2700K, Energy Star Listed, Dimmable, Omini Direction Type

#### Certification

ETL/cETL Listed



### LED Type, Dimmable

Model	Input Voltage	Input Wattage	LED Lamp	LED CT / CRI	Lamp Lumen (TYP)	Finish	Shade	Dimension (OD x H x H1 max)
P607D-05-E26	120V	8W	ST21	2700K / >80	800	Black	Clear Glass	10.0" x 9.9" x 36.0"

Note: H1- Hanging Cable Length, Adjustable