

Project Name:



Notes:

PT-DLS-R-FR-6I-15W-5CCT


Type:

6" 2-HR Fire Rated Slim Downlight with CCT Selector Date:

Portor's 2-hour fire-rated recessed downlight is an exceptional lighting solution designed to prioritize safety without compromising on aesthetics or functionality. This innovative fixture is engineered to withstand the rigors of a fire for up to two hours, making it an essential choice for commercial and residential applications where fire protection is paramount.

Ideal for soffits, drop ceilings, closets, attics, hallways, bathrooms, kitchens, basements, entry ways, porches (covered ceiling only), garages, stairwells, corridors, nursing/retirement homes, condos, elevators, apartments, and any other small areas with limited space.





FEATURES

- 2-Hour fire rating providing a reinforced and heat resistant steel casing
- LED technology fits anywhere you need general light source
- IC rated for direct contact with insulation
- Perfect solution where joists or duct work would normally prevent recessed installation
- · Wet location rated for soffit applications
- Easy installation, no housing required

DIMMING

Triac dimmable down to 100%-10%. Compatible with most major brands of dimmers.

LISTING

ETL Listed, Wet location, Energy Star Listed











WATTAGE	DELIVERED LUMENS	EFFICACY	
15W	1104 @ 2700K	up to 74 lm/W	
	1050 @ 3000K		
	1103 @ 3500K		
	1111 @ 4000K		
	1077 @ 5000K		

TECHNICAL SPECIFICATION

WATTAGE	15W
VOLTAGE	120V, 60 Hz
CCT	27K/30K/35K/40K/50K
CRI	90
BEAM ANGLE	120°
RATING	Suitable for wet locations
DIMMABLE	Triac dimming
POWER FACTOR	>0.9
OPERATING TEMP	-4°F~104°F (20~40°C)
WARRANTY	5 year limited

MODEL NUMBER(S)						
MODEL#	WATTS	LUMENS	LM/WATT	CCT	CRI	VOLTAGE
PT-DLS-R-FR-6I-15W-5CCT	15W	1111 (at 4000K)	74	2700K/3000K/3500K/ 4000K/5000K	90	120V





PT-DLS-R-FR-6I-15W-5CCT

6" 2-HR Fire Rated Slim Downlight with CCT Selector





Sealing gasket standard




PROVIDING A REINFORCED AND HEAT RESISTANT STEEL CASING

Tested to comply with UL 263, **ASTM E119 & CAN ULC S101**



Change color temperature with the simple flip of a switch

DIMENSION



MOUNTING OPTIONS



UNI-DLS 4"/6" Universal Slim LED Housing for New Construction



RP-DLS-6I 6" Slim LED Rough plate

COMPATIBLE DIMMERS

LUTRON*	LEVITON*	LEGRAND
• CT-600P	• RNL06	• ADTP70TU
• DVLC-153P	• 6672	
MSCL-OP153M	• 6674	
• PD-6WCL	• IPL06	
• MACL-153M/MA-R	• DLS06	
• TG-600PR-WH	• SELV-300P-WH	
• S-600PR-WH	• VP106-1LZ	
• CTCL-153PDH-WH		
• TGCL-153PH-LA		
• SLV-600P-AL		
• DV-600PR-WH		
• SCL-153PH-WH		

^{*}For more details, please visit company's website



www.portorlighting.com