

Resistor™ II

METAL DETECTABLE



CORDED METAL DETECTABLE REUSABLE FLANGED PLUGS



Tested to ANSI S3.19-1974 standards, this metal detectable earplug has an NRR of 27. Its tapered design and sturdy stem allow for easy insertion and removal and a comfortable fit in the ear canal. Made from soft thermoplastic rubber, the FP43-FMD is non-irritating to the skin and washable in mild soap and water. It is available in box (100 Box) and case quantities.



Washable
In mild soap
and water

Four Flanges
For a safe, accurate,
and comfortable seal

Metal Detectable
Plug and Cord

Reusable Soft
Thermoplastic Rubber
Provides superior comfort
and protection



RESISTOR™ II FP43-FMD - CORDED	
Style	Reusable
Material	Soft Thermoplastic Rubber
NRR	27
Shape	4 Flange Tapered
Color	Blue
Dielectric	No
Size	Regular
Cord	Black TPE
Packaging	100 Box / 1000 Case
Origin	Made in Taiwan

ATTENUATION DATA • TABLA DE ATENUACIÓN • DONNÉES D'ATTÉNUATION									
Tested According to ANSI Specs S3.19-1974 Probado de Acuerdo a las Especificaciones ANSI S3.19-1974 Tests Conformes aux Spécs ANSI S3.19-1974									
Frequency (Hz) Frecuencia (Hz) Fréquence (Hz)	125	250	500	1000	2000	3150	4000	6300	8000
Mean Attenuation (dB) Atenuación Media (dB) Atténuation Moyenne (dB)	32.3	31.9	33.8	36.5	35.4	38.8	39.2	43.4	44.3
Standard Deviation (dB) Desviación Standard (dB) Ecart Standard (dB)	4.0	3.8	4.0	3.8	3.3	4.0	4.9	4.7	3.1

Meets ANSI S3.19-1974 Standards.

www.radians.com



HEADQUARTERS

5305 Distriplex Farms Drive
Memphis, TN 38141
Toll Free: 877-723-4267
Phone: 901-388-7776 / Fax: 901-266-2558