

## RUST-OLUEM® CHALKED ULTRA MATTE SPRAYS

## **DESCRIPTION AND USES**

Rust-Oleum<sup>®</sup> Chalked Ultra Matte Sprays create an ultra matte finish with excellent coverage and adhesion on furniture and home décor. Chalked Ultra Matte Sprays provide one coat coverage on most surfaces without special surface preparation or priming. It can be painted or distressed, giving the project a one of a kind look. It is suitable for use on wood, metal, ceramic, glass, canvas and more.

Chalked Ultra Matte Sprays feature an advanced spray system that allows you to spray at any angle, even upside down for those hard to reach areas. A comfort spray tip with a wider finger pad to reduce fatigue caused by continuous spraying.

**TIP:** Some plastics made of polyethylene such as plastic storage containers are manufactured in a way that may hinder maximum paint adhesion. Test paint in a hidden area first.

## **PRODUCTS**

SKU	DESCRIPTION (Aerosol)	
302590	Charcoal	
302591	Linen White	
302592	Aged Gray	
302593	Country Gray	
302594	Blush Pink	
302595	Serenity Blue	
302596	Chiffon Cream	
302597	Tidal Pond	
302598	Coastal Blue	
302599	Matte Clear	
329193	Farmhouse Red	
329194	Cocoa Bean	
374163	Tate Green	
374164	Blue Harbor	

## PRODUCT APPLICATION

## READ ALL DIRECTIONS BEFORE BEGNNING PROJECT

Use outdoors or in a well-ventilated area such as an open garage. Use when temperature is between 50°F (10°C) and 90°F (32°C) and humidity is below 65% to ensure proper drying. Avoid spraying in very windy and dusty conditions. Cover surrounding area to protect from spray mist.

## **SURFACE PREPARATION**

Remove all dirt, grease, oil, salt and chemical contaminants by washing the surface with soap and water and let dry. Remove loose paint and rust with a wire brush or sandpaper. Lightly sand glossy surfaces. Remove any wax by lightly wiping the surface with mineral spirits.

## PRODUCT APPLICATION (cont.)

#### **SURFACE PREPARATION (cont.)**

WARNING! If you scrape, sand or remove old paint from any surface, you may release lead paint dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE; ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. . Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

#### **PRIMING**

Priming is not required for most surfaces. For excellent coverage, use of a Rust-Oleum primer can be used on surfaces such as bare wood and treated wood.

#### **APPLICATION**

Shake can vigorously for one minute after the mixing ball begins to rattle. If mixing ball fails to rattle DO NOT STRIKE CAN. Contact Rust-Oleum. Shake often during use. Hold can upright 10-12" from the surface and spray in a steady back-and-forth motion, slightly overlapping each stroke. Keep the can the same distance from the surface. Keep the can in motion while spraying. Apply 2 or more light coats a few minutes apart. Do not use near open flame.

#### **DRY & RECOAT**

Dry and recoat times are based on 70°F (21°C) and 50% relative humidity. Allow more time at cooler temperatures. Dries to the touch in 20 minutes and is dry to handle in 1 hour. May be recoated in 1 hour or after 48 hours. The finish coat is fully dry in 24 hours. NOTE: On plastic, maximum paint adhesion and durability is achieved in 5-7 days. Apply Chalked Clear Protective Topcoat over any Chalked Paint colors for added protection. Apply according to the label instructions.

#### DISTRESSING

This paint can be distressed if desired. To distress the surface, lightly sand the surface with fine to medium grit sandpaper or a sanding sponge. Wait 2 hours before sanding or distressing.

#### **CLEAN-UP**

Wipe off tip before storing. Clean-up wet paint with xylene or mineral spirits. Properly discard empty container. Do not burn or place in home trash compactor.

### **CLOGGING**

If the valve clogs, twist and pull off spray tip and rinse in a solvent such as mineral spirits. Do not insert any object into can valve opening.

Form: GDH-1027 Rev.: 031622



# RUST-OLUEM® CHALKED ULTRA MATTE SPRAYS

## PHYSICAL PROPERTIES

		CHALKED SPRAYS
Resin Type		Acrylic Modified Alkyd
Pigment Type		Varies with color
Solvents		Acetone, Mineral Spirits, Naptha
MIR		0.80 Max
Weight		12 ounces.
Recommended Dry Film Thickness (DFT) per Coat		1-2 mils (25-50μ)
Practical Coverage at Recommended DFT (assume 15% material loss)		12 sq.ft./can (0.3 m²/can)
Dry Times at 77°F (25°C) and 50% Relative Humidity	Touch	20 minutes
	Handle	1 hour
	Recoat	Within 1 hour or after 48 hours
Shelf Life		5 years
Flash Point		-156°F (-104°C)
Safety Information		For additional information, see SDS

Calculated values are shown and may vary from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.



Phone: 800-481-4785 www.rustoleum.com

Form: GDH-1027 Rev.: 031622