










12V LED AREA LIGHTS – SOLID COPPER

E18

LED AREA LIGHTS

:: Catalog No.	LA-010-CR	LA-118-CR	LA-112-CR
:: Housing / Finish	Solid Copper, Natural Finish		
:: Wattage	3W		
:: Lumens	200LM		
:: Voltage	12V AC/DC		
:: Color Temp	3000K Warm White		
:: Beam Angle	360°		
:: Light Source	Integrated SMD LED Tower		
:: Lens	Heavy-Duty Clear PC Lens		
:: Diameter of Shade	5-3/4"	6-1/4"	6-1/4"
:: Height of Stem	20"	18"	12"
:: Total Height			
:: Accessories included	 Silicon-filled WireNuts  8-1/2" Non-metallic Spike  3ft. SPT-2 18AWG Lead Wire  LED Tower  WET Location  IP67  5 YEAR WARRANTY		

