


## LLHB2



Shown with Optional Sensor (not included)

## TECHNICAL SPECIFICATIONS:

- :: New Generation Linear High Bay Fixture
- :: In Excess of 140 Lumens per Watt
- :: Slim Aluminum Housing for better heat dissipation and longer life
- :: Surface Mounting Kit included
- :: Optic Polycarbonate Lens
- :: Includes 3 Ft. Adjustable Suspension Kit
- :: Offers Plug-&-Play Programmable Bi-Level PIR Motion Sensor Kit and Emergency Backup Options
- :: Driver: Towin
- :: Input Voltage: 100V~277V AC
- :: Efficacy: 140LM/W
- :: Beam angle: 90°
- :: Ambient Temperature: -40°F~122°F
- :: Dimmable
















## LED LINEAR HIGH BAYS

CATALOG NO.	WATTS	LUMENS	COLOR TEMP	DIMENSIONS
LLHB2-100W-50K-D	100W	14000LM	5000K	23-3/4"(L) x 15-1/8"(W) x 2-7/8"(H)
LLHB2-100W-40K-D	100W	14000LM	4000K	
LLHB2-150W-50K-D	150W	21000LM	5000K	34-3/4"(L) x 15-1/8"(W) x 2-7/8"(H)
LLHB2-150W-40K-D	150W	21000LM	4000K	
LLHB2-200W-50K-D	200W	28000LM	5000K	45-7/8"(L) x 15-1/8"(W) x 2-7/8"(H)
LLHB2-200W-40K-D	200W	28000LM	4000K	
SK618	Plug-&-Play Programmable Bi-Level PIR Motion Sensor Kit			
LLHB2-100W-EB	Emergency Backup Kit for LLHB2-100W, ≥90 mins. Operation			
LLHB2-150W-EB	Emergency Backup Kit for LLHB2-150W, 290 mins. Operation			
LLHB2-200W-EB	Emergency Backup Kit for LLHB2-200W, ≥90 mins. Operation			