

LPNG-1X4

TECHNICAL SPECIFICATIONS:

:: External driver mounted on top

:: High efficiency: 105LM/W

:: Input Voltage: AC100V-277V

:: Fixture Operating Voltage: 36VDC

:: Color Rendering Index: Ra>80

:: Dimmable: 0~10V dimming

:: Power Factor: >0.9

:: Current (mA): 1050mA 36V DC

:: Frequency Range: 50Hz~60Hz

:: Total harmonic distortion: ≤20 %

:: Operating temperature: 68°F~104°F

:: Rated life: 50,000 hrs.

:: 5-year warranty

FEATURES:

:: Soft and wide light emitting

:: No infrared rays, no ultraviolet radiation, no thermal effect

:: No flickering, no humming, no RF interference

:: Earthquake hooks and Suspension hooks preinstalled






















LED BACKLIT PANEL LIGHTS (1X4)

CATALOG NO.	WATTS	LUMENS	COLOR TEMP	DIMENSIONS
LPNG-1X4-4KLM-50K-D	40W	4200LM	5000K	
LPNG-1X4-4KLM-40K-D	40W	4200LM	4000K	47.8" x 11.81" x 1.69"
LPNG-1X4-4KLM-35K-D	40W	4200LM	3500K	
LPNG-1X4-4KLM-27K-D	40W	4200LM	2700K	