LWP2



TECHNICAL SPECIFICATIONS:

- :: Full cutoff, dark sky compliant
- :: Die-cast aluminum with powder coat finish (Dark Bronze)
- :: Philips Lumileds Lexeon 3030 high flux LED
- :: TIR optic lens TYPE II
- :: 120~277V
- :: Includes mounting hardware
- :: Redesigned for high-performance LED
- :: CRI: >80
- :: Power Factor: 95%
- :: Operating Temp:-4°F to 104°F
- :: 70,000 hour rated life
- :: 7-year warranty
- :: Suitable for Wet Locations, IP54

APPLICATIONS:

- :: Ideal for general site lighting, alleys, loading docks, doorway, pathway and parking areas.
- :: Replace existing HID flood lights/ wall packs
- :: Great for use with motion sensors or other instant on/off controls






























LED FULL CUTOFF WALL PACK

CATALOG NO.	WATTS	LUMENS	COLOR TEMP	REPLACEMENT RANGE	DIMENSIONS
LWP2-50-CW	50W	5700LM	5000K	175~250 MH	14" (w) x 9-1/4" (H) x 8-1/4" (D)
LWP2-50-WW	50W	5600LM	3000K	175~250 MH	
LWP2-80-CW	80W	9100LM	5000K	320~400 MH	
LWP2-80-WW	80W	8700LM	3000K	320~400 MH	





