

PL3

120V
Internal Drivers

TECHNICAL SPECIFICATIONS:

- :: Built-in LED driver
- :: Surface or Recessed Mount
- :: Color Temperature: 3000K
- :: Available in three colors: white, brushed nickel, black
- :: Durable polycarbonate housing
- :: Clear acrylic lens
- :: 4-watt LED board, 275 lumens with internal driver
- :: Working voltage: 120V AC
- :: Includes 6 ft. power cord with 15A plug (120V) and rotary switch
- :: Each puck comes with pre-installed 10-inch linkable cord

FEATURES:

- :: Energy efficient under cabinet light
- :: Low heat, easy installation, environmentally friendly, maintenance free for many years
- :: Ideal for under cabinet, display cases or in low profile areas



LED-PL3WHT



LED-PL3NKL



LED-PL3BLK



ACCESSORIES INCLUDED



For recessed application, housing can be easily removed.

120-VOLT LED 3-PACK PUCK LIGHTS

CATALOG NO.	DESCRIPTION	WATTS	LED QTY	LUMENS	DIMENSIONS
LED-PL3WHT	3 Lights 120V, Plastic, White	3 x 4W	3 x 8	3 x 275LM	2-1/2" (dia) x 1-1/8" (D)
LED-PL3NKL	3 Lights 120V, Plastic, Brushed Nickel	3 x 4W	3 x 8	3 x 275LM	
LED-PL3BLK	3 Lights 120V, Plastic, Black	3 x 4W	3 x 8	3 x 275LM	

