

JOB NAME: _____

DATE: _____

TYPE: _____



DIMENSIONS:

L 18.1" X W 7.9" X H 7.9"

ACCESSORIES INCLUDED:



6 Foot plug-in cord included with Transformers

TR-600W-MT-SS

MULTI-TAP (12V/13V/14V/15V AC) LAND-SCAPE TRANSFORMERS

ELECTRICAL SPECIFICATIONS:

- Voltage: 120V/60Hz
- Wattage: 600W MAX
- Output Voltage: 120V

HOUSING SPECIFICATIONS:

- Finish: Stainless Steel
- Terminal Blocks: 2
- Suitable for Indoor and Outdoor use
- Dual Protection:
 - Primary circuit protection: Auto Reset Thermal Circuit Breaker On Core
 - Secondary circuit protection: (1) 25A Magnetic Circuit Breaker
- IP Rating: IP67, Suitable for Wet Locations

CERTIFICATIONS:



MODEL	WATTS	VOLTAGE
TR-600W-MT-SS	600W	120V

ACCESSORIES INCLUDED:



TR-MTMR



TR-DTMR



TR-PC

MODEL	DESCRIPTION
TR-MTMR	24-Hour 3-Prong Mechanical Plug-in Timer
TR-DTMR	7-Day 3-Prong Digital Plug-in Timer
TR-PC	Photocell with Plug-in Molex Connector

WARRANTY: 3 years

